

## Label printers with a centered material guide - M series



### Material guide centered



Basic version



Peel-off version P

### The accurate and versatile one

for printing on all materials that are wound on rolls or reels or fanfold - especially very small labels or slim continuous materials such as pressed shrink tubes.

As regards the label width, no adjustment of the plungers is needed.

Width-adapted print rollers are provided for slim materials.

1.4	Label printer		SQUIX 4.3 M		SQUIX 4 M	
	Printable resolution	dpi	203	300	300	600
	Print speed	up to mm/s	250	250	300	150
	Print width	up to mm	104	108.4	105.7	105.7

## Differences compared to a left-aligned material guide

### 1 Ribbon holder

Easy insertion of the ribbons is enabled with the three-part tightening axes. A preprinted ruler simplifies the adjustment.

### 2 Roll holder

When setting the margin stop, the material roll is automatically centered. If rolls with 100 mm core diameter are processed, an adapter is recommended.

### 3 Plungers

Both plungers are fixed for all material widths. No print head settings or adjustments are necessary.

### 4 Material guide

The material guide just in front of the print roller provides accurate imprint. The material width is adjusted with a spindle.

### Slim print rollers

To achieve accurate imprint with slim materials and ribbons slim print rollers are needed. These prevent from print roller wear, print head contamination and errors during material feed.

Coating: synthetic rubber



Label printer SQUIX 4 MP

